


Cascade SUMMIT200

200 mm Semi-automated Probe System



“The new SUMMIT200 advanced probing system enables up to 5X faster time to accurate data.”



Versatile microscope mount

- High stability or large area
- Boom stand for low power optics
- Gross Z lift with repeatable focus for easy access to probes
- Manual or programmable
- Field-upgradable

Connection panels

- Coaxial, triaxial, and pin jack feed-troughs available
- Limit cable strain and motion for measurement stability
- Instrument stays connected to back of panel
- Probe connection made at front of panel
- Simple to re-arrange cabling when needed

Platen lift

- Easy and safe contact and separate function for probe cards and positioners
- Available micrometer adjustment to set probe card contact
- Probe and device safety interlock

TopHat™

- New TopHat covers for easier and higher-accuracy probe setup
- Allows full access to positioners and microscope at any temperature
- Allows probe adjustments without exposing wafer and chamber to external environment
- ProbeView window for probe and device visibility

PureLine™ technology

- Enhanced EMI-shielding
- Lowest spectral noise floor and system AC noise
- Ideal for low-level and 1/f measurements

AttoGuard®

- Extends instrument guard to completely surround wafer
- Makes the station invisible to the instrument
- Extremely low capacitance and leakage characteristics
- Fast settling times

MicroChamber®

- EMI-shielding for low-noise measurements
- Environmentally sealed for moisture-free, low-temperature measurements
- Low volume for the fastest purge
- Light-tight to eliminate the need for a dark box

MicroChamber access door

- Auto-locking door to protect wafers at cold temperatures
- Full width for easy access to wafers and cal substrates
- Hardware interlock to protect user from hazardous chuck bias voltage

Rollout stage

- Full wafer access for safe and easy loading
- Maintains chuck integrity without contaminating layers
- Easy access to calibration substrates on auxiliary chucks
- New Lift pin technology for fast manual load/unload of hot wafers

eVue™ IV Digital Imaging System

- Fast probe set-up with wide field-of-view and single objective in MicroChamber
- Easy navigation with multiple live video views of probes and wafer
- New high-speed focus system for faster and accurate die stepping
- New safety features for probes and usability

Velox™ probe station control software

- Innovative operating software for advanced prober operation, temperature control, z-profiling and stepping
- Wafer mapping, automated wafer alignment, and auto XYZ and theta correction for sub-micron stepping

WinCal XE™ RF Calibration Software

- Comprehensive and intuitive on-wafer RF measurement calibration software
- Achieve the most accurate and repeatable calibrations every time
- Supports advanced calibration algorithms, e.g. LRRM, eLRRM, Hybrid LRRM, SOLR
- Supports up to 12 VNA ports

Auxiliary chucks

- Up to 3 integrated multi-purpose mounts (calibration, cleaning, contact)
- New microwave absorber and material options (ceramic, steel)
- Thermally isolated to prevent load drift over temperature
- Automated probe cleaning capabilities
- Optional probe alignment fiducial

Chuck vacuum control

- Independent zones for various wafer sizes, dies and shards
- Easy access controls for auxiliary chucks

Modular chucks

- FemtoGuard® triaxial and coax versions available
- MicroVac option for thin wafer support and best thermal conductivity
- High-performance thermal and economical non-thermal options
- Wide range of temperature options from -60 °C to 300 °C and higher

Manual mode stage control

- Intuitive manual chuck XY stage controls in semi-automatic engineering mode
- Safe mode: automatically disables manual controls in automation mode

Precision 200 mm wafer stage

- New user-selectable performance modes for standard, fast and high accuracy
- Increased test throughput with up to 100 mm/sec. speed
- High reliability 24/7 operation

Contact Intelligence™ Technology

- Integrated HTS (High Thermal Stability) reduces probe drift and thermal soak time
- Optional ReAlign for SUMMIT200 with Near-On-Axis PTPA technology, enabling vertical probe cards on smallest footprint with highest thermal stability
- Optional VueTrack™ enables fast time to data even when measuring over a large thermal range
- Enables unattended test over multiple temperatures

Scalable system

- In-field upgradable wafer loading and automation
- Add test accuracy improvements for increased test performance

Compact small footprint

- Integrated vibration isolation for reliable small pad probing
- Integrated system electronics with power loss wafer safety protection



©Copyright 2018, FormFactor, Inc. All rights reserved. FormFactor and the FormFactor logo are trademarks of FormFactor, Inc. All other trademarks are the property of their respective owners. All information is subject to change without notice.